


TS8100 Series

Progressive Cavity PC Pump

Spare Parts Guide



Item	Part Number	Description
1	8100-100-007	Cable Assembly
2	7509-0340	Motor Sleeve
3	2800-0903	M3 x 6mm Set Screw
4	7509-0610	Flexible Coupling
5	3300-0586	U-Seal (x2)
6	2800-0836	M2.5 x 3mm Set Screw
*7	8100-100-001	Rotor, TS8100-100
	8100-200-001	Rotor, TS8100-200
	8100-300-001	Rotor, TS8100-300
	8100-400-001	Rotor, TS8100-400
	8100-500-001	Rotor, TS8100-500
8	8100-MPLATE	Motor Mount Plate, Inc. Pin
9	2800-0295	Washer, M2.5, Lock, SS (x4)
10	8100-100-005	Stator Housing
*11	8100-100-002	Stator, TS8100-100
	8100-200-002	Stator, TS8100-200
	8100-300-002	Stator, TS8100-300
	8100-400-002	Stator, TS8100-400
	8100-500-002	Stator, TS8100-500
12	7509-0090	Lock Nut
13	7090-0030	Locking Cap, TE and TT
14	8100-100-006	Stator Cap Bottom
15	2800-0897	M2.5 x 14mm Socket Screw (x4)
16	2800-0917	Washer #4 NAS 620 (x4)
17	3300-0616	Vent Shaft O-Ring, Small
18	3300-0617	Vent Shaft O-Ring, Large
19	7509-0570	Vent Screw
20	2800-0901	M3 x 6mm Machine Screw (x3)
21	8100-100-004	Motor
22	2800-0900	4-20 x 1/4" Forming Screw (x3)
23	8100-CLEANKIT	Cleaning Kit (Not Shown)
24	TS8100-SYBRACKET	Syringe Bracket (Not Shown)
25	TS8100-MBRACKET	Mounting Bracket (Not Shown)

Note: When refitting stator (11), wet the rotor (7) by applying the dispensing fluid, or appropriate lube that is compatible with the dispensing fluid, to the rotor surface.

TS8100-SPG-20220119

**For Sales
and Support:**

Techcon Corporate Headquarters

10800 Valley View Street, Cypress,
Cypress, California, 90630, USA

Tel: 1-714-799-9910 | Fax: 1-714-828-2001

E-mail: eorders@okinternational.com

Visit our website for more information and to contact the Techcon office nearest you. We have several offices worldwide that are ready to serve your needs.

techcon.com/contact-us

